

## 2024 Pacific Cup PCER: ANCHOR APPENDIX

Instructions: For the chain material you wish to use, select the size in a row with a LOA *and* displacement greater than or equal to that of your vessel. For the nylon rode, select the diameter in a row with a LOA *and* displacement greater than or equal to that of your vessel. Where blank, go to the next higher size.

Max LOA	Max Disp	Proof Coil	BBB Galv	Stainless	BBB SS	Hi Test	SS Wt/10ft	Rode Dia
26	2900	3/16"	3/16"					3/8"
31	5200			3/16"			4	3/8"
34	6700	1/4"	1/4"					7/16"
41	12300	5/16"	5/16"					1/2"
44	14800			1/4"			6	1/2"
46	16900				1/4"			9/16"
48	19000	3/8"				1/4"		9/16"
49	20700		3/8"	5/16"			8	9/16"
54	27200				5/16"			5/8"
57	32300	7/16"				5/16"		5/8"
62	41900	1/2"	1/2"	3/8"	3/8"		14	3/4"
69	56900					3/8"		3/4"
77	82200	5/8"		1/2"			23	7/8"
86	112400				1/2"	1/2"		7/8"
96	156500	3/4"		5/8"			36	Call
106	212600					5/8"		Call
120	302600			3/4"			55	Call
133	411700					3/4"		Call